

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204996

Luminaire Tested: **LD6B20D010 EU6B10209035 6LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204996  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10209035 6LBCSMMS1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1816.0 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204996

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P204996

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204996

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.6	4.3
10°-20°	220.5	12.1
20°-30°	322.1	17.7
30°-40°	368.4	20.3
40°-50°	354.0	19.5
50°-60°	273.4	15.1
60°-70°	152.6	8.4
70°-80°	44.4	2.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.2	34.2
0°-40°	989.6	54.5
0°-60°	1617.1	89.0
0°-90°	1816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1816.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	834	
5°	827	79
15°	782	221
25°	700	322
35°	590	368
45°	462	354
55°	307	273
65°	153	153
75°	39	44
85°	1	2
90°	0	



TEST NUMBER: P204996

CATALOG NUMBER: LD6B20D010 EU6B10209035 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	834.0
2.5°	834.0
5°	826.9
7.5°	823.4
10°	811.6
12.5°	797.5
15°	782.3
17.5°	767.0
20°	744.7
22.5°	727.1
25°	700.1
27.5°	673.0
30°	646.0
32.5°	619.0
35°	589.6
37.5°	560.3
40°	526.2
42.5°	495.7
45°	461.6
47.5°	422.8
50°	386.4
52.5°	346.5
55°	306.6
57.5°	265.5
60°	226.7
62.5°	187.9
65°	152.7
67.5°	119.8
70°	89.3
72.5°	62.3
75°	38.8
77.5°	20.0
80°	7.0
82.5°	2.3
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)