

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205397

Luminaire Tested: **LD6B20D010 EU6B10208050 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208050 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2275.0 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205397

CATALOG NUMBER: LD6B20D010 EU6B10208050 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205397

CATALOG NUMBER: LD6B20D010 EU6B10208050 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89	89	89	89	89	89		
	2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77	77	77	77	77	77		
	3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68	68	68	68	68	68		
	4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60	60	60	60	60	60		
	5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53	53	53	53	53	53		
	6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47	47	47	47	47	47		
	7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43	43	43	43	43	43		
	8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39	39	39	39	39	39		
	9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36	36	36	36	36	36		
	10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33	33	33	33	33	33		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205397

CATALOG NUMBER: LD6B20D010 EU6B10208050 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	5.8
10°-20°	336.8	14.8
20°-30°	429.5	18.9
30°-40°	445.4	19.6
40°-50°	410.4	18.0
50°-60°	308.7	13.6
60°-70°	166.7	7.3
70°-80°	44.7	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.5	39.5
0°-40°	1343.9	59.1
0°-60°	2063.0	90.7
0°-90°	2275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2275.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1436	
5°	1414	132
15°	1201	337
25°	933	429
35°	711	445
45°	534	410
55°	346	309
65°	167	167
75°	39	45
85°	0	1
90°	0	



TEST NUMBER: P205397

CATALOG NUMBER: LD6B20D010 EU6B10208050 6LBSL11

CANDELA DISTRIBUTION (FULL):

	0°
0°	1435.6
2.5°	1430.8
5°	1413.9
7.5°	1382.4
10°	1326.9
12.5°	1271.3
15°	1201.2
17.5°	1135.9
20°	1068.3
22.5°	998.2
25°	932.9
27.5°	870.1
30°	812.1
32.5°	758.9
35°	710.6
37.5°	664.6
40°	621.1
42.5°	575.2
45°	534.1
47.5°	488.2
50°	442.3
52.5°	393.9
55°	345.6
57.5°	297.3
60°	251.4
62.5°	207.9
65°	166.8
67.5°	128.1
70°	94.3
72.5°	65.3
75°	38.7
77.5°	16.9
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)