

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204220

Luminaire Tested: **LD6B60D010TE EU6B60709027 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709027 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5108.6 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204220

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204220

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		93	92	90
2	102	96	90	85		100	94	88	84		90	86	82		87	83	80		84	81	79
3	95	85	78	73		92	84	77	72		81	75	71		78	74	70		76	72	69
4	87	77	69	63		85	75	68	63		73	67	62		71	65	61		69	64	60
5	81	69	61	55		79	68	61	55		66	60	55		64	59	54		63	58	53
6	75	63	55	49		73	62	54	49		60	54	49		59	53	48		57	52	48
7	70	58	50	44		68	57	49	44		55	49	44		54	48	43		53	47	43
8	65	53	45	40		64	52	45	40		51	44	39		50	44	39		49	43	39
9	61	49	41	36		60	48	41	36		47	40	36		46	40	36		45	40	35
10	58	45	38	33		56	45	38	33		44	37	33		43	37	33		42	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204220

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.3	4.9
10°-20°	680.2	13.3
20°-30°	944.6	18.5
30°-40°	1030.8	20.2
40°-50°	961.6	18.8
50°-60°	729.9	14.3
60°-70°	399.7	7.8
70°-80°	110.0	2.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1875.1	36.7
0°-40°	2906.0	56.9
0°-60°	4597.5	90.0
0°-90°	5108.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5108.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2672	
5°	2649	250
15°	2424	680
25°	2053	945
35°	1648	1031
45°	1249	962
55°	816	730
65°	399	400
75°	96	110
85°	0	2
90°	0	



TEST NUMBER: P204220

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2671.8
2.5°	2671.8
5°	2649.3
7.5°	2615.5
10°	2564.9
12.5°	2497.4
15°	2424.3
17.5°	2334.3
20°	2249.9
22.5°	2148.7
25°	2053.1
27.5°	1957.4
30°	1850.6
32.5°	1749.3
35°	1648.1
37.5°	1546.8
40°	1451.2
42.5°	1350.0
45°	1248.7
47.5°	1147.5
50°	1035.0
52.5°	928.1
55°	815.6
57.5°	708.7
60°	601.9
62.5°	495.0
65°	399.4
67.5°	309.4
70°	230.6
72.5°	157.5
75°	95.6
77.5°	45.0
80°	11.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)