

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203039

Luminaire Tested: **LD6B20D010 EU6B10209050 6LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203039  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10209050 6LBWB1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 999.1 lumens  
Efficiency: N/A  
Efficacy: 48.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203039

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203039

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70																
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64																
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59			59																
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54			54																
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50																
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46			46																
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42			42																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203039

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBWB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.8	7.1
10°-20°	198.0	19.8
20°-30°	277.3	27.8
30°-40°	264.8	26.5
40°-50°	150.8	15.1
50°-60°	36.8	3.7
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.1	54.7
0°-40°	810.9	81.2
0°-60°	998.6	100.0
0°-90°	999.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	999.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	753	
5°	747	71
15°	702	198
25°	606	277
35°	431	265
45°	193	151
55°	37	37
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203039

CATALOG NUMBER: LD6B20D010 EU6B10209050 6LBWB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	753.0
2.5°	753.0
5°	746.9
7.5°	738.8
10°	732.6
12.5°	720.4
15°	702.1
17.5°	685.8
20°	665.5
22.5°	639.0
25°	606.5
27.5°	569.8
30°	529.1
32.5°	480.3
35°	431.4
37.5°	372.4
40°	309.3
42.5°	250.3
45°	193.3
47.5°	142.5
50°	99.7
52.5°	63.1
55°	36.6
57.5°	16.3
60°	4.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)