

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205007

Luminaire Tested: **LD6B30D010 EU6B30509027 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509027 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2496.4 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205007

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205007

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205007

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.0	4.3
10°-20°	303.2	12.1
20°-30°	442.8	17.7
30°-40°	506.4	20.3
40°-50°	486.7	19.5
50°-60°	375.8	15.1
60°-70°	209.8	8.4
70°-80°	61.0	2.4
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.0	34.2
0°-40°	1360.4	54.5
0°-60°	2223.0	89.0
0°-90°	2496.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2496.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1146	
5°	1137	108
15°	1075	303
25°	962	443
35°	811	506
45°	635	487
55°	421	376
65°	210	210
75°	53	61
85°	2	3
90°	0	



TEST NUMBER: P205007

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1146.4
2.5°	1146.4
5°	1136.7
7.5°	1131.9
10°	1115.7
12.5°	1096.4
15°	1075.4
17.5°	1054.4
20°	1023.7
22.5°	999.5
25°	962.3
27.5°	925.2
30°	888.1
32.5°	850.9
35°	810.6
37.5°	770.2
40°	723.4
42.5°	681.4
45°	634.6
47.5°	581.3
50°	531.2
52.5°	476.3
55°	421.4
57.5°	364.9
60°	311.6
62.5°	258.3
65°	209.9
67.5°	164.7
70°	122.7
72.5°	85.6
75°	53.3
77.5°	27.4
80°	9.7
82.5°	3.2
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)