

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202881

Luminaire Tested: **LD6B60D010TE EU6B60709027 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202881
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709027 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4484.7 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202881

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWWH1

Luminous Intensity Polar Plot






TEST NUMBER: P202881

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	71	64	59	80	71	64	59	69	63	59		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	54	49	71	61	54	49	59	53	49		58	53	49		57
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53
10	64	53	46	42	63	53	46	42	52	46	42		51	45	42		50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202881

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.8	6.0
10°-20°	796.2	17.8
20°-30°	1198.5	26.7
30°-40°	1225.4	27.3
40°-50°	744.2	16.6
50°-60°	209.6	4.7
60°-70°	31.9	0.7
70°-80°	10.4	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2262.5	50.4
0°-40°	3487.9	77.8
0°-60°	4441.7	99.0
0°-90°	4484.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4484.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2786	
5°	2797	268
15°	2819	796
25°	2617	1199
35°	1986	1225
45°	957	744
55°	208	210
65°	28	32
75°	11	10
85°	0	1
90°	0	



TEST NUMBER: P202881

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2785.5
2.5°	2785.5
5°	2796.8
7.5°	2813.7
10°	2813.7
12.5°	2824.9
15°	2819.3
17.5°	2808.0
20°	2768.6
22.5°	2712.4
25°	2616.7
27.5°	2509.8
30°	2363.5
32.5°	2189.0
35°	1986.4
37.5°	1761.4
40°	1502.5
42.5°	1232.4
45°	956.6
47.5°	709.0
50°	500.8
52.5°	337.6
55°	208.2
57.5°	123.8
60°	61.9
62.5°	39.4
65°	28.1
67.5°	22.5
70°	16.9
72.5°	11.3
75°	11.3
77.5°	5.6
80°	5.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)