

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204813

Luminaire Tested: **LD6B40D010 EU6B30509024 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509024 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3315.8 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204813

CATALOG NUMBER: LD6B40D010 EU6B30509024 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204813

CATALOG NUMBER: LD6B40D010 EU6B30509024 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204813

CATALOG NUMBER: LD6B40D010 EU6B30509024 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	3.9
10°-20°	365.3	11.0
20°-30°	549.5	16.6
30°-40°	651.2	19.6
40°-50°	648.1	19.5
50°-60°	522.4	15.8
60°-70°	316.1	9.5
70°-80°	117.3	3.5
80°-90°	17.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.1	31.5
0°-40°	1694.3	51.1
0°-60°	2864.8	86.4
0°-90°	3315.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3315.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1354	
5°	1348	128
15°	1294	365
25°	1194	550
35°	1043	651
45°	844	648
55°	583	522
65°	318	316
75°	106	117
85°	14	17
90°	0	



TEST NUMBER: P204813

CATALOG NUMBER: LD6B40D010 EU6B30509024 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1354.2
2.5°	1354.2
5°	1348.2
7.5°	1344.2
10°	1332.1
12.5°	1312.1
15°	1294.0
17.5°	1273.9
20°	1249.8
22.5°	1225.7
25°	1193.5
27.5°	1159.3
30°	1121.2
32.5°	1085.0
35°	1042.8
37.5°	998.6
40°	946.4
42.5°	896.1
45°	843.9
47.5°	785.6
50°	721.3
52.5°	655.0
55°	582.7
57.5°	518.4
60°	446.1
62.5°	381.8
65°	317.5
67.5°	257.2
70°	200.9
72.5°	150.7
75°	106.5
77.5°	68.3
80°	40.2
82.5°	24.1
85°	14.1
87.5°	6.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)