

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203504

Luminaire Tested: **LD6B60D010TE EU6B60709727 6LBMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203504  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B60D010TE EU6B60709727 6LBMB1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1857.1 lumens  
Efficiency: N/A  
Efficacy: 29.7 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203504

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBMB1

### Luminous Intensity Polar Plot






TEST NUMBER: P203504

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 111 | 109 | 106 |  | 111 | 109 | 107 | 105 |  | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  | 97  | 96  |
| 2   | 108 | 104 | 100 | 96  |  | 106 | 102 | 98  | 95  |  | 99  | 96  | 93  |  | 96  | 93  | 91  |  | 93  | 91  | 89  |
| 3   | 103 | 97  | 92  | 88  |  | 101 | 95  | 91  | 87  |  | 93  | 89  | 86  |  | 90  | 87  | 85  |  | 88  | 86  | 83  |
| 4   | 98  | 91  | 85  | 81  |  | 96  | 90  | 85  | 81  |  | 87  | 83  | 80  |  | 85  | 82  | 79  |  | 84  | 81  | 78  |
| 5   | 93  | 85  | 79  | 75  |  | 92  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 73  |
| 6   | 89  | 80  | 74  | 70  |  | 87  | 79  | 74  | 70  |  | 78  | 73  | 69  |  | 76  | 72  | 69  |  | 75  | 71  | 68  |
| 7   | 84  | 75  | 69  | 65  |  | 83  | 75  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 67  | 64  |
| 8   | 80  | 71  | 65  | 61  |  | 79  | 71  | 65  | 61  |  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 63  | 60  |
| 9   | 77  | 67  | 61  | 58  |  | 76  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  | 60  | 57  |  | 64  | 60  | 57  |
| 10  | 73  | 64  | 58  | 54  |  | 72  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  | 57  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203504

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBMB1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 212.1  | 11.4      |
| 10°-20°   | 523.5  | 28.2      |
| 20°-30°   | 630.5  | 33.9      |
| 30°-40°   | 398.8  | 21.5      |
| 40°-50°   | 91.2   | 4.9       |
| 50°-60°   | 1.0    | 0.1       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1366.0 | 73.6      |
| 0°-40°    | 1764.8 | 95.0      |
| 0°-60°    | 1857.1 | 100.0     |
| 0°-90°    | 1857.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1857.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2338 |      |
| 5°  | 2285 | 212  |
| 15° | 1868 | 523  |
| 25° | 1397 | 630  |
| 35° | 629  | 399  |
| 45° | 101  | 91   |
| 55° | 0    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P203504

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBMB1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2337.9 |
| 2.5°  | 2328.3 |
| 5°    | 2285.1 |
| 7.5°  | 2203.5 |
| 10°   | 2102.7 |
| 12.5° | 1982.7 |
| 15°   | 1867.5 |
| 17.5° | 1757.1 |
| 20°   | 1641.8 |
| 22.5° | 1526.6 |
| 25°   | 1397.0 |
| 27.5° | 1243.4 |
| 30°   | 1056.2 |
| 32.5° | 844.9  |
| 35°   | 628.9  |
| 37.5° | 446.5  |
| 40°   | 302.4  |
| 42.5° | 187.2  |
| 45°   | 100.8  |
| 47.5° | 43.2   |
| 50°   | 9.6    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)