

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204122

Luminaire Tested: **LD6B60D010TE EU6B60709727 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709727 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3078.9 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204122

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBNMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204122

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	103	109	106	103	101	102	100	98		98	97	95		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		77	73	69		75
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	59	80	70	63	59	68	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54
10	65	54	47	43	64	54	47	43	53	47	43		52	46	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204122

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.5	7.6
10°-20°	621.5	20.2
20°-30°	829.7	26.9
30°-40°	669.4	21.7
40°-50°	320.8	10.4
50°-60°	190.2	6.2
60°-70°	126.4	4.1
70°-80°	67.7	2.2
80°-90°	18.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1685.7	54.8
0°-40°	2355.1	76.5
0°-60°	2866.1	93.1
0°-90°	3078.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3078.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2525	
5°	2496	234
15°	2212	621
25°	1816	830
35°	1072	669
45°	396	321
55°	210	190
65°	127	126
75°	64	68
85°	15	19
90°	0	



TEST NUMBER: P204122

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBNMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2525.0
2.5°	2525.0
5°	2495.7
7.5°	2446.7
10°	2378.2
12.5°	2304.8
15°	2211.8
17.5°	2123.8
20°	2025.9
22.5°	1923.1
25°	1815.5
27.5°	1702.9
30°	1541.4
32.5°	1316.3
35°	1071.7
37.5°	846.6
40°	655.7
42.5°	508.9
45°	396.4
47.5°	313.2
50°	264.2
52.5°	234.9
55°	210.4
57.5°	190.8
60°	166.4
62.5°	146.8
65°	127.2
67.5°	107.7
70°	93.0
72.5°	78.3
75°	63.6
77.5°	48.9
80°	39.1
82.5°	29.4
85°	14.7
87.5°	4.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)