

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203055

Luminaire Tested: **LD6B40D010 EU6B30508027 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508027 6LBWB1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2248.1 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203055

CATALOG NUMBER: LD6B40D010 EU6B30508027 6LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P203055

CATALOG NUMBER: LD6B40D010 EU6B30508027 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70																
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64																
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59			59																
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54			54																
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50																
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46			46																
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42			42																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203055

CATALOG NUMBER: LD6B40D010 EU6B30508027 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.3	7.1
10°-20°	445.5	19.8
20°-30°	624.0	27.8
30°-40°	595.9	26.5
40°-50°	339.4	15.1
50°-60°	82.9	3.7
60°-70°	1.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1228.8	54.7
0°-40°	1824.7	81.2
0°-60°	2247.0	100.0
0°-90°	2248.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2248.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1694	
5°	1680	159
15°	1580	445
25°	1365	624
35°	971	596
45°	435	339
55°	82	83
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203055

CATALOG NUMBER: LD6B40D010 EU6B30508027 6LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1694.3
2.5°	1694.3
5°	1680.5
7.5°	1662.2
10°	1648.5
12.5°	1621.0
15°	1579.8
17.5°	1543.2
20°	1497.4
22.5°	1437.9
25°	1364.6
27.5°	1282.2
30°	1190.6
32.5°	1080.7
35°	970.8
37.5°	838.0
40°	696.0
42.5°	563.2
45°	435.0
47.5°	320.5
50°	224.4
52.5°	142.0
55°	82.4
57.5°	36.6
60°	9.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)