

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204742

Luminaire Tested: **LD6B60D010TE EU6B60709727 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709727 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4632.9 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204742

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204742

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204742

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.9	3.8
10°-20°	504.1	10.9
20°-30°	759.3	16.4
30°-40°	903.4	19.5
40°-50°	901.8	19.5
50°-60°	733.4	15.8
60°-70°	451.2	9.7
70°-80°	174.8	3.8
80°-90°	28.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1440.3	31.1
0°-40°	2343.7	50.6
0°-60°	3978.9	85.9
0°-90°	4632.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4632.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1867	
5°	1861	177
15°	1790	504
25°	1652	759
35°	1447	903
45°	1172	902
55°	821	733
65°	453	451
75°	159	175
85°	22	28
90°	0	



TEST NUMBER: P204742

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1866.6
2.5°	1869.4
5°	1861.1
7.5°	1850.1
10°	1836.4
12.5°	1811.7
15°	1789.8
17.5°	1756.8
20°	1721.1
22.5°	1688.2
25°	1652.5
27.5°	1603.1
30°	1553.7
32.5°	1507.0
35°	1446.6
37.5°	1380.7
40°	1320.4
42.5°	1246.2
45°	1172.1
47.5°	1092.5
50°	1007.4
52.5°	919.6
55°	820.8
57.5°	724.7
60°	631.4
62.5°	540.8
65°	452.9
67.5°	370.6
70°	293.7
72.5°	222.3
75°	159.2
77.5°	104.3
80°	63.1
82.5°	38.4
85°	22.0
87.5°	11.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)