

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204711

Luminaire Tested: **LD6B40D010 EU6B30509027 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204711  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B40D010 EU6B30509027 6LBPSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3727.0 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204711

CATALOG NUMBER: LD6B40D010 EU6B30509027 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204711

CATALOG NUMBER: LD6B40D010 EU6B30509027 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204711

CATALOG NUMBER: LD6B40D010 EU6B30509027 6LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.3	3.8
10°-20°	405.6	10.9
20°-30°	610.8	16.4
30°-40°	726.8	19.5
40°-50°	725.5	19.5
50°-60°	590.0	15.8
60°-70°	363.0	9.7
70°-80°	140.6	3.8
80°-90°	22.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1158.6	31.1
0°-40°	1885.4	50.6
0°-60°	3200.9	85.9
0°-90°	3727.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3727.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1502	
5°	1497	142
15°	1440	406
25°	1329	611
35°	1164	727
45°	943	725
55°	660	590
65°	364	363
75°	128	141
85°	18	23
90°	0	



TEST NUMBER: P204711

CATALOG NUMBER: LD6B40D010 EU6B30509027 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1501.6
2.5°	1503.8
5°	1497.2
7.5°	1488.3
10°	1477.3
12.5°	1457.4
15°	1439.8
17.5°	1413.3
20°	1384.6
22.5°	1358.1
25°	1329.3
27.5°	1289.6
30°	1249.9
32.5°	1212.3
35°	1163.7
37.5°	1110.7
40°	1062.2
42.5°	1002.5
45°	942.9
47.5°	878.9
50°	810.4
52.5°	739.8
55°	660.3
57.5°	583.0
60°	507.9
62.5°	435.0
65°	364.4
67.5°	298.1
70°	236.3
72.5°	178.9
75°	128.1
77.5°	83.9
80°	50.8
82.5°	30.9
85°	17.7
87.5°	8.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)