

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202886

Luminaire Tested: **LD6B60D010TE EU6B60709727 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709727 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3900.0 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202886

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202886

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	71	64	59	80	71	64	59	69	63	59		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	54	49	71	61	54	49	59	53	49		58	53	49		57
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53
10	64	53	46	42	63	53	46	42	52	46	42		51	45	42		50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202886

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.8	6.0
10°-20°	692.4	17.8
20°-30°	1042.3	26.7
30°-40°	1065.7	27.3
40°-50°	647.2	16.6
50°-60°	182.2	4.7
60°-70°	27.7	0.7
70°-80°	9.0	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1967.5	50.4
0°-40°	3033.1	77.8
0°-60°	3862.6	99.0
0°-90°	3900.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3900.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2422	
5°	2432	233
15°	2452	692
25°	2276	1042
35°	1727	1066
45°	832	647
55°	181	182
65°	24	28
75°	10	9
85°	0	1
90°	0	



TEST NUMBER: P202886

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2422.3
2.5°	2422.3
5°	2432.1
7.5°	2446.8
10°	2446.8
12.5°	2456.5
15°	2451.6
17.5°	2441.9
20°	2407.6
22.5°	2358.7
25°	2275.5
27.5°	2182.5
30°	2055.3
32.5°	1903.6
35°	1727.4
37.5°	1531.7
40°	1306.6
42.5°	1071.7
45°	831.9
47.5°	616.6
50°	435.5
52.5°	293.6
55°	181.1
57.5°	107.7
60°	53.8
62.5°	34.3
65°	24.5
67.5°	19.6
70°	14.7
72.5°	9.8
75°	9.8
77.5°	4.9
80°	4.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)