

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203777

Luminaire Tested: **LD6B40D010 EU6B30508030 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508030 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2814.4 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203777

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203777

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89		
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83		
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79		
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74		
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70		
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66		
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203777

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	467.7	16.6
10°-20°	898.8	31.9
20°-30°	817.1	29.0
30°-40°	495.3	17.6
40°-50°	112.8	4.0
50°-60°	14.4	0.5
60°-70°	6.5	0.2
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2183.6	77.6
0°-40°	2678.8	95.2
0°-60°	2806.0	99.7
0°-90°	2814.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2814.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5526	
5°	5209	468
15°	3237	899
25°	1772	817
35°	785	495
45°	124	113
55°	14	14
65°	5	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P203777

CATALOG NUMBER: LD6B40D010 EU6B30508030 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5525.5
2.5°	5458.4
5°	5209.4
7.5°	4807.2
10°	4294.9
12.5°	3763.4
15°	3236.7
17.5°	2757.9
20°	2355.7
22.5°	2030.1
25°	1771.6
27.5°	1541.8
30°	1316.7
32.5°	1053.4
35°	785.2
37.5°	550.6
40°	363.9
42.5°	225.0
45°	124.5
47.5°	57.5
50°	23.9
52.5°	19.2
55°	14.4
57.5°	14.4
60°	9.6
62.5°	9.6
65°	4.8
67.5°	4.8
70°	4.8
72.5°	4.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)