

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252831

Luminaire Tested: **LD6B60D010TE EU6B60708030 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708030 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7598.0 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252831

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252831

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	97	91	87		101	95	90	86		91	87	84		88	85	82		85	83	80
3	96	87	81	76		94	86	80	75		83	78	74		81	76	72		78	74	71
4	90	80	72	67		87	78	72	66		76	70	66		74	69	65		72	68	64
5	84	73	65	60		82	72	65	60		70	64	59		68	63	58		66	62	58
6	78	67	60	54		77	66	59	54		65	58	54		63	57	53		62	57	53
7	74	62	55	49		72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	58	50	45		68	57	50	45		56	49	45		55	49	45		53	48	44
9	65	54	46	42		64	53	46	42		52	46	41		51	45	41		50	45	41
10	62	50	43	39		61	50	43	39		49	43	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	339988
5°	336867
10°	329447
15°	318988
20°	306106
25°	287357
30°	248660
35°	193607
40°	147149
45°	114712
50°	95143
55°	85387
60°	77741
65°	71737
70°	65923
75°	61077
80°	55229
85°	50527



TEST NUMBER: P252831

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.5	6.4
10°-20°	1326.9	17.5
20°-30°	1807.2	23.8
30°-40°	1529.3	20.1
40°-50°	981.1	12.9
50°-60°	675.1	8.9
60°-70°	461.2	6.1
70°-80°	256.6	3.4
80°-90°	75.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3619.7	47.6
0°-40°	5149.0	67.8
0°-60°	6805.1	89.6
0°-90°	7598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5211	
5°	5144	486
15°	4723	1327
25°	3992	1807
35°	2431	1529
45°	1243	981
55°	751	675
65°	465	461
75°	242	257
85°	68	75
90°	0	



TEST NUMBER: P252831

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5211.3
2.5°	5191.5
5°	5143.8
7.5°	5068.3
10°	4973.0
12.5°	4853.8
15°	4722.8
17.5°	4571.8
20°	4409.0
22.5°	4226.3
25°	3991.9
27.5°	3674.1
30°	3300.8
32.5°	2871.8
35°	2430.9
37.5°	2045.6
40°	1727.8
42.5°	1461.7
45°	1243.3
47.5°	1072.5
50°	937.4
52.5°	834.1
55°	750.7
57.5°	671.3
60°	595.8
62.5°	528.3
65°	464.7
67.5°	401.2
70°	345.6
72.5°	290.0
75°	242.3
77.5°	194.6
80°	147.0
82.5°	107.2
85°	67.5
87.5°	27.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)