

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205020

Luminaire Tested: **LD6B40D010 EU6B30509030 6LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205020  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B40D010 EU6B30509030 6LBCSMMS1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3669.5 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205020

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P205020

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205020

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.8	4.3
10°-20°	445.6	12.1
20°-30°	650.9	17.7
30°-40°	744.4	20.3
40°-50°	715.4	19.5
50°-60°	552.5	15.1
60°-70°	308.3	8.4
70°-80°	89.7	2.4
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.3	34.2
0°-40°	1999.7	54.5
0°-60°	3267.6	89.0
0°-90°	3669.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3669.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1685	
5°	1671	159
15°	1581	446
25°	1415	651
35°	1192	744
45°	933	715
55°	620	552
65°	308	308
75°	78	90
85°	2	4
90°	0	



TEST NUMBER: P205020

CATALOG NUMBER: LD6B40D010 EU6B30509030 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1685.1
2.5°	1685.1
5°	1670.9
7.5°	1663.8
10°	1640.0
12.5°	1611.5
15°	1580.7
17.5°	1549.8
20°	1504.7
22.5°	1469.1
25°	1414.6
27.5°	1360.0
30°	1305.4
32.5°	1250.8
35°	1191.5
37.5°	1132.1
40°	1063.3
42.5°	1001.6
45°	932.8
47.5°	854.4
50°	780.9
52.5°	700.2
55°	619.5
57.5°	536.4
60°	458.1
62.5°	379.7
65°	308.5
67.5°	242.1
70°	180.4
72.5°	125.8
75°	78.3
77.5°	40.3
80°	14.2
82.5°	4.7
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)