

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202670

Luminaire Tested: **LD6B60D010TE EU6B60708030 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708030 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4685.1 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202670

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202670

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	73		80	76	72		79	75	71		77	74	71
6	87	78	72	67		85	77	71	67		76	71	67		74	70	66		73	69	66
7	83	73	67	63		81	72	67	63		71	66	62		70	65	62		69	65	61
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	58
9	75	65	59	55		73	64	59	55		63	58	54		62	58	54		62	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202670

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.2	10.2
10°-20°	1227.6	26.2
20°-30°	1507.8	32.2
30°-40°	1033.9	22.1
40°-50°	332.3	7.1
50°-60°	67.4	1.4
60°-70°	26.5	0.6
70°-80°	9.9	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3213.5	68.6
0°-40°	4247.4	90.7
0°-60°	4647.1	99.2
0°-90°	4685.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4685.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5210	
5°	5111	478
15°	4392	1228
25°	3326	1508
35°	1649	1034
45°	393	332
55°	68	67
65°	28	26
75°	8	10
85°	0	2
90°	0	



TEST NUMBER: P202670

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5210.2
2.5°	5178.4
5°	5110.8
7.5°	4983.7
10°	4812.8
12.5°	4602.1
15°	4391.5
17.5°	4157.0
20°	3898.7
22.5°	3628.5
25°	3326.4
27.5°	2992.6
30°	2571.3
32.5°	2106.3
35°	1649.3
37.5°	1232.0
40°	886.2
42.5°	604.1
45°	393.4
47.5°	242.4
50°	147.0
52.5°	91.4
55°	67.6
57.5°	51.7
60°	39.7
62.5°	31.8
65°	27.8
67.5°	19.9
70°	15.9
72.5°	11.9
75°	7.9
77.5°	7.9
80°	4.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)