

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203891

Luminaire Tested: **LD6B40D010 EU6B30509730 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30509730 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1568.6 lumens
Efficiency: N/A
Efficacy: 37.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203891

CATALOG NUMBER: LD6B40D010 EU6B30509730 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203891

CATALOG NUMBER: LD6B40D010 EU6B30509730 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203891

CATALOG NUMBER: LD6B40D010 EU6B30509730 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.6	11.0
10°-20°	425.7	27.1
20°-30°	515.8	32.9
30°-40°	351.5	22.4
40°-50°	83.7	5.3
50°-60°	13.1	0.8
60°-70°	4.9	0.3
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1114.0	71.0
0°-40°	1465.5	93.4
0°-60°	1562.3	99.6
0°-90°	1568.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1568.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1907	
5°	1853	173
15°	1524	426
25°	1127	516
35°	562	351
45°	89	84
55°	14	13
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203891

CATALOG NUMBER: LD6B40D010 EU6B30509730 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1906.6
2.5°	1895.9
5°	1853.0
7.5°	1795.7
10°	1713.4
12.5°	1620.4
15°	1523.9
17.5°	1423.7
20°	1323.5
22.5°	1223.4
25°	1126.8
27.5°	1037.4
30°	908.6
32.5°	740.5
35°	561.6
37.5°	400.6
40°	264.7
42.5°	164.5
45°	89.4
47.5°	46.5
50°	25.0
52.5°	17.9
55°	14.3
57.5°	10.7
60°	7.2
62.5°	7.2
65°	3.6
67.5°	3.6
70°	3.6
72.5°	3.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)