

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203906

Luminaire Tested: **LD6B60D010TE EU6B60708030 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708030 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3003.6 lumens
Efficiency: N/A
Efficacy: 48.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203906

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203906

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	108	106	111	109	106	104		105	103	101			101	100	98			94
2	108	103	99	96	106	101	98	95		98	95	93			95	93	91			87
3	103	96	91	87	101	95	90	87		92	88	85			90	87	84			81
4	97	90	84	80	96	89	84	80		87	82	79			85	81	78			76
5	93	84	78	74	91	83	78	74		82	77	73			80	76	73			70
6	88	79	73	69	86	78	73	69		77	72	68			75	71	68			66
7	84	74	68	64	82	74	68	64		72	67	64			71	67	63			62
8	80	70	64	60	78	69	64	60		68	63	60			67	63	59			58
9	76	66	60	56	75	66	60	56		65	60	56			64	59	56			54
10	72	63	57	53	71	62	57	53		61	56	53			61	56	53			51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203906

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.5	11.0
10°-20°	815.2	27.1
20°-30°	987.6	32.9
30°-40°	673.1	22.4
40°-50°	160.3	5.3
50°-60°	25.1	0.8
60°-70°	9.3	0.3
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2133.3	71.0
0°-40°	2806.3	93.4
0°-60°	2991.6	99.6
0°-90°	3003.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3003.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3651	
5°	3548	331
15°	2918	815
25°	2158	988
35°	1075	673
45°	171	160
55°	27	25
65°	7	9
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203906

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3651.0
2.5°	3630.5
5°	3548.3
7.5°	3438.7
10°	3281.1
12.5°	3103.0
15°	2918.1
17.5°	2726.3
20°	2534.5
22.5°	2342.7
25°	2157.7
27.5°	1986.5
30°	1739.9
32.5°	1417.9
35°	1075.4
37.5°	767.2
40°	506.9
42.5°	315.1
45°	171.2
47.5°	89.0
50°	47.9
52.5°	34.2
55°	27.4
57.5°	20.5
60°	13.7
62.5°	13.7
65°	6.8
67.5°	6.8
70°	6.8
72.5°	6.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)