

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252837

Luminaire Tested: **LD6B60D010TE EU6B60709030 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709030 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6488.9 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252837

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252837

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	97	91	87	101	95	90	86	91	87	84		88	85	82		85
3	96	87	81	76	94	86	80	75	83	78	74		81	76	72		78
4	90	80	72	67	87	78	72	66	76	70	66		74	69	65		72
5	84	73	65	60	82	72	65	60	70	64	59		68	63	58		66
6	78	67	60	54	77	66	59	54	65	58	54		63	57	53		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		53
9	65	54	46	42	64	53	46	42	52	46	41		51	45	41		50
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290366
5°	287697
10°	281358
15°	272424
20°	261423
25°	245411
30°	212365
35°	165349
40°	125670
45°	97966
50°	81258
55°	72921
60°	66389
65°	61270
70°	56291
75°	52153
80°	47151
85°	43191



TEST NUMBER: P252837

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.7	6.4
10°-20°	1133.3	17.5
20°-30°	1543.4	23.8
30°-40°	1306.0	20.1
40°-50°	837.9	12.9
50°-60°	576.5	8.9
60°-70°	393.9	6.1
70°-80°	219.1	3.4
80°-90°	64.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3091.4	47.6
0°-40°	4397.4	67.8
0°-60°	5811.8	89.6
0°-90°	6488.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6488.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4451	
5°	4393	415
15°	4033	1133
25°	3409	1543
35°	2076	1306
45°	1062	838
55°	641	577
65°	397	394
75°	207	219
85°	58	64
90°	0	



TEST NUMBER: P252837

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4450.7
2.5°	4433.7
5°	4393.0
7.5°	4328.6
10°	4247.1
12.5°	4145.4
15°	4033.4
17.5°	3904.5
20°	3765.4
22.5°	3609.4
25°	3409.2
27.5°	3137.9
30°	2819.0
32.5°	2452.6
35°	2076.1
37.5°	1747.0
40°	1475.6
42.5°	1248.4
45°	1061.8
47.5°	915.9
50°	800.6
52.5°	712.4
55°	641.1
57.5°	573.3
60°	508.8
62.5°	451.2
65°	396.9
67.5°	342.6
70°	295.1
72.5°	247.6
75°	206.9
77.5°	166.2
80°	125.5
82.5°	91.6
85°	57.7
87.5°	23.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)