

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203574

Luminaire Tested: **LD6B40D010 EU6B30508050 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508050 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3468.6 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203574

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203574

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203574

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.1	6.9
10°-20°	640.4	18.5
20°-30°	859.9	24.8
30°-40°	705.3	20.3
40°-50°	423.6	12.2
50°-60°	281.5	8.1
60°-70°	188.7	5.4
70°-80°	101.5	2.9
80°-90°	28.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1739.3	50.1
0°-40°	2444.7	70.5
0°-60°	3149.7	90.8
0°-90°	3468.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3468.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2588	
5°	2545	239
15°	2282	640
25°	1894	860
35°	1119	705
45°	536	424
55°	311	281
65°	191	189
75°	96	102
85°	24	29
90°	0	



TEST NUMBER: P203574

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2588.1
2.5°	2569.0
5°	2545.1
7.5°	2492.4
10°	2430.2
12.5°	2353.7
15°	2281.9
17.5°	2195.8
20°	2109.7
22.5°	2014.0
25°	1894.4
27.5°	1750.9
30°	1559.6
32.5°	1344.3
35°	1119.4
37.5°	928.1
40°	765.4
42.5°	636.3
45°	535.8
47.5°	454.5
50°	397.1
52.5°	349.2
55°	311.0
57.5°	277.5
60°	248.8
62.5°	215.3
65°	191.4
67.5°	162.7
70°	138.7
72.5°	114.8
75°	95.7
77.5°	76.5
80°	57.4
82.5°	43.1
85°	23.9
87.5°	9.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)