

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205423

Luminaire Tested: **LD6B40D010 EU6B30508050 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B40D010 EU6B30508050 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4662.7 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205423

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205423

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205423

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	5.8
10°-20°	690.3	14.8
20°-30°	880.2	18.9
30°-40°	912.8	19.6
40°-50°	841.1	18.0
50°-60°	632.7	13.6
60°-70°	341.5	7.3
70°-80°	91.6	2.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1841.6	39.5
0°-40°	2754.4	59.1
0°-60°	4228.2	90.7
0°-90°	4662.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4662.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2942	
5°	2898	271
15°	2462	690
25°	1912	880
35°	1456	913
45°	1095	841
55°	708	633
65°	342	342
75°	79	92
85°	0	1
90°	0	



TEST NUMBER: P205423

CATALOG NUMBER: LD6B40D010 EU6B30508050 6LBSL11

CANDELA DISTRIBUTION (FULL):

0°	
0°	2942.4
2.5°	2932.5
5°	2897.8
7.5°	2833.4
10°	2719.5
12.5°	2605.6
15°	2461.9
17.5°	2328.2
20°	2189.5
22.5°	2045.8
25°	1912.1
27.5°	1783.3
30°	1664.4
32.5°	1555.4
35°	1456.3
37.5°	1362.2
40°	1273.1
42.5°	1178.9
45°	1094.7
47.5°	1000.6
50°	906.5
52.5°	807.4
55°	708.4
57.5°	609.3
60°	515.2
62.5°	426.0
65°	341.8
67.5°	262.5
70°	193.2
72.5°	133.7
75°	79.3
77.5°	34.7
80°	9.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)