

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204118

Luminaire Tested: **LD6B60D010TE EU6B60709030 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204118  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B60D010TE EU6B60709030 6LBNMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3681.3 lumens  
Efficiency: N/A  
Efficacy: 58.9 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204118

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204118

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 112 | 108 | 105 | 103 |  | 109 | 106 | 103 | 101 |  | 102 | 100 | 98  |  | 98  | 97  | 95  |  | 95  | 93  | 92  |
| 2   | 105 | 99  | 94  | 90  |  | 102 | 97  | 92  | 89  |  | 94  | 90  | 87  |  | 91  | 87  | 85  |  | 88  | 85  | 83  |
| 3   | 98  | 90  | 84  | 79  |  | 96  | 89  | 83  | 79  |  | 86  | 81  | 77  |  | 84  | 80  | 76  |  | 81  | 78  | 75  |
| 4   | 92  | 83  | 76  | 71  |  | 90  | 82  | 76  | 71  |  | 80  | 74  | 70  |  | 77  | 73  | 69  |  | 75  | 71  | 68  |
| 5   | 87  | 77  | 70  | 64  |  | 85  | 76  | 69  | 64  |  | 74  | 68  | 64  |  | 72  | 67  | 63  |  | 70  | 66  | 62  |
| 6   | 81  | 71  | 64  | 59  |  | 80  | 70  | 63  | 59  |  | 68  | 63  | 58  |  | 67  | 62  | 58  |  | 66  | 61  | 57  |
| 7   | 77  | 66  | 59  | 54  |  | 75  | 65  | 59  | 54  |  | 64  | 58  | 54  |  | 63  | 57  | 53  |  | 61  | 57  | 53  |
| 8   | 72  | 61  | 55  | 50  |  | 71  | 61  | 54  | 50  |  | 60  | 54  | 49  |  | 59  | 53  | 49  |  | 58  | 53  | 49  |
| 9   | 69  | 58  | 51  | 46  |  | 67  | 57  | 51  | 46  |  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  | 49  | 46  |
| 10  | 65  | 54  | 47  | 43  |  | 64  | 54  | 47  | 43  |  | 53  | 47  | 43  |  | 52  | 46  | 43  |  | 51  | 46  | 43  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204118

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBNMW1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 280.3  | 7.6       |
| 10°-20°   | 743.1  | 20.2      |
| 20°-30°   | 992.1  | 26.9      |
| 30°-40°   | 800.4  | 21.7      |
| 40°-50°   | 383.6  | 10.4      |
| 50°-60°   | 227.4  | 6.2       |
| 60°-70°   | 151.1  | 4.1       |
| 70°-80°   | 81.0   | 2.2       |
| 80°-90°   | 22.3   | 0.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2015.5 | 54.8      |
| 0°-40°    | 2815.9 | 76.5      |
| 0°-60°    | 3426.8 | 93.1      |
| 0°-90°    | 3681.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3681.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3019 |      |
| 5°  | 2984 | 280  |
| 15° | 2645 | 743  |
| 25° | 2171 | 992  |
| 35° | 1281 | 800  |
| 45° | 474  | 384  |
| 55° | 252  | 227  |
| 65° | 152  | 151  |
| 75° | 76   | 81   |
| 85° | 18   | 22   |
| 90° | 0    |      |



TEST NUMBER: P204118

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3019.0 |
| 2.5°  | 3019.0 |
| 5°    | 2983.9 |
| 7.5°  | 2925.4 |
| 10°   | 2843.5 |
| 12.5° | 2755.7 |
| 15°   | 2644.6 |
| 17.5° | 2539.3 |
| 20°   | 2422.2 |
| 22.5° | 2299.4 |
| 25°   | 2170.7 |
| 27.5° | 2036.1 |
| 30°   | 1843.0 |
| 32.5° | 1573.9 |
| 35°   | 1281.3 |
| 37.5° | 1012.2 |
| 40°   | 784.0  |
| 42.5° | 608.5  |
| 45°   | 473.9  |
| 47.5° | 374.5  |
| 50°   | 315.9  |
| 52.5° | 280.8  |
| 55°   | 251.6  |
| 57.5° | 228.2  |
| 60°   | 198.9  |
| 62.5° | 175.5  |
| 65°   | 152.1  |
| 67.5° | 128.7  |
| 70°   | 111.2  |
| 72.5° | 93.6   |
| 75°   | 76.1   |
| 77.5° | 58.5   |
| 80°   | 46.8   |
| 82.5° | 35.1   |
| 85°   | 17.6   |
| 87.5° | 5.9    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)