

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203183

Luminaire Tested: **LD6B50D010TE EU6B30509730 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203183  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B50D010TE EU6B30509730 6LBWMW1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3771.4 lumens  
Efficiency: N/A  
Efficacy: 64.2 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203183

CATALOG NUMBER: LD6B50D010TE EU6B30509730 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203183

CATALOG NUMBER: LD6B50D010TE EU6B30509730 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203183

CATALOG NUMBER: LD6B50D010TE EU6B30509730 6LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	199.5	5.3
10°-20°	559.3	14.8
20°-30°	805.9	21.4
30°-40°	836.8	22.2
40°-50°	618.6	16.4
50°-60°	369.5	9.8
60°-70°	224.6	6.0
70°-80°	123.0	3.3
80°-90°	34.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1564.7	41.5
0°-40°	2401.5	63.7
0°-60°	3389.7	89.9
0°-90°	3771.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3771.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2118	
5°	2104	199
15°	1985	559
25°	1756	806
35°	1349	837
45°	796	619
55°	402	370
65°	224	225
75°	114	123
85°	27	34
90°	0	



TEST NUMBER: P203183

CATALOG NUMBER: LD6B50D010TE EU6B30509730 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2117.9
2.5°	2117.9
5°	2104.2
7.5°	2085.9
10°	2058.4
12.5°	2026.4
15°	1985.2
17.5°	1939.5
20°	1893.8
22.5°	1829.7
25°	1756.5
27.5°	1678.8
30°	1578.1
32.5°	1477.5
35°	1349.4
37.5°	1216.8
40°	1070.4
42.5°	928.6
45°	795.9
47.5°	677.0
50°	571.8
52.5°	480.3
55°	402.5
57.5°	343.1
60°	292.8
62.5°	256.2
65°	224.1
67.5°	196.7
70°	169.2
72.5°	141.8
75°	114.4
77.5°	91.5
80°	68.6
82.5°	50.3
85°	27.4
87.5°	13.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)