

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203379

Luminaire Tested: **LD6B50D010TE EU6B30508035 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508035 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4327.4 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203379

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203379

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94	94	94		
	2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87	87	87	87	87	87		
	3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81	81	81		
	4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76	76	76		
	5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71	71	71		
	6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66	66	66	66	66	66		
	7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62	62	62	62	62	62		
	8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58	58	58	58	58	58		
	9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55	55	55	55	55	55		
	10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52	52	52	52	52	52		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203379

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	493.5	11.4
10°-20°	1211.6	28.0
20°-30°	1401.9	32.4
30°-40°	896.1	20.7
40°-50°	254.1	5.9
50°-60°	45.3	1.0
60°-70°	18.5	0.4
70°-80°	6.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3107.0	71.8
0°-40°	4003.1	92.5
0°-60°	4302.5	99.4
0°-90°	4327.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4327.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5398	
5°	5302	494
15°	4345	1212
25°	3094	1402
35°	1414	896
45°	295	254
55°	42	45
65°	18	19
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P203379

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5398.5
2.5°	5392.5
5°	5302.2
7.5°	5139.7
10°	4911.0
12.5°	4646.2
15°	4345.3
17.5°	4032.4
20°	3725.4
22.5°	3424.5
25°	3093.5
27.5°	2732.4
30°	2329.1
32.5°	1877.8
35°	1414.3
37.5°	1023.1
40°	710.2
42.5°	469.4
45°	294.9
47.5°	174.5
50°	102.3
52.5°	60.2
55°	42.1
57.5°	36.1
60°	30.1
62.5°	24.1
65°	18.1
67.5°	12.0
70°	12.0
72.5°	6.0
75°	6.0
77.5°	6.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)