

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204846

Luminaire Tested: **LD6B60D010TE EU6B60709730 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709730 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4896.5 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204846

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBSCMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204846

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	110	106	102	99		108	104	100	97		100	97	94		96	93	91		92	90	89
2	101	94	87	82		99	92	86	81		88	84	79		85	81	78		82	79	76
3	93	83	75	70		90	81	74	69		79	73	68		76	71	67		73	69	65
4	85	74	66	60		83	73	65	59		70	64	58		68	62	58		66	61	57
5	79	66	58	52		77	65	57	51		63	56	51		61	55	50		60	54	50
6	73	60	52	45		71	59	51	45		57	50	45		56	49	44		54	49	44
7	68	55	46	40		66	54	46	40		52	45	40		51	44	40		50	44	39
8	63	50	42	36		61	49	41	36		48	41	36		47	40	36		46	40	35
9	59	46	38	33		57	45	38	32		44	37	32		43	37	32		42	36	32
10	55	42	35	30		54	42	34	30		41	34	29		40	34	29		39	33	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204846

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	3.9
10°-20°	539.4	11.0
20°-30°	811.5	16.6
30°-40°	961.7	19.6
40°-50°	957.1	19.5
50°-60°	771.5	15.8
60°-70°	466.7	9.5
70°-80°	173.3	3.5
80°-90°	25.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1540.4	31.5
0°-40°	2502.1	51.1
0°-60°	4230.7	86.4
0°-90°	4896.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4896.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2000	
5°	1991	189
15°	1911	539
25°	1762	811
35°	1540	962
45°	1246	957
55°	860	772
65°	469	467
75°	157	173
85°	21	26
90°	0	



TEST NUMBER: P204846

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1999.9
2.5°	1999.9
5°	1991.0
7.5°	1985.1
10°	1967.3
12.5°	1937.6
15°	1910.9
17.5°	1881.2
20°	1845.6
22.5°	1810.0
25°	1762.5
27.5°	1712.1
30°	1655.7
32.5°	1602.3
35°	1540.0
37.5°	1474.7
40°	1397.6
42.5°	1323.4
45°	1246.2
47.5°	1160.2
50°	1065.2
52.5°	967.3
55°	860.5
57.5°	765.5
60°	658.7
62.5°	563.8
65°	468.8
67.5°	379.8
70°	296.7
72.5°	222.5
75°	157.3
77.5°	100.9
80°	59.3
82.5°	35.6
85°	20.8
87.5°	8.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)