

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203173

Luminaire Tested: **LD6B50D010TE EU6B30508035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508035 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5181.5 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203173

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203173

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203173

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.0	5.3
10°-20°	768.5	14.8
20°-30°	1107.3	21.4
30°-40°	1149.6	22.2
40°-50°	849.9	16.4
50°-60°	507.7	9.8
60°-70°	308.5	6.0
70°-80°	169.0	3.3
80°-90°	47.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2149.8	41.5
0°-40°	3299.4	63.7
0°-60°	4657.1	89.9
0°-90°	5181.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5181.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2910	
5°	2891	274
15°	2728	768
25°	2413	1107
35°	1854	1150
45°	1094	850
55°	553	508
65°	308	308
75°	157	169
85°	38	47
90°	0	



TEST NUMBER: P203173

CATALOG NUMBER: LD6B50D010TE EU6B30508035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2909.8
2.5°	2909.8
5°	2890.9
7.5°	2865.8
10°	2828.1
12.5°	2784.1
15°	2727.5
17.5°	2664.7
20°	2601.8
22.5°	2513.9
25°	2413.3
27.5°	2306.5
30°	2168.2
32.5°	2029.9
35°	1854.0
37.5°	1671.7
40°	1470.6
42.5°	1275.8
45°	1093.5
47.5°	930.1
50°	785.6
52.5°	659.9
55°	553.1
57.5°	471.3
60°	402.2
62.5°	351.9
65°	307.9
67.5°	270.2
70°	232.5
72.5°	194.8
75°	157.1
77.5°	125.7
80°	94.3
82.5°	69.1
85°	37.7
87.5°	18.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)