

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205135

Luminaire Tested: **LD6B50D010TE EU6B30509035 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509035 6LBMLI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4143.0 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205135
CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205135

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																																				
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																																				
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																																				
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																																				
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																																				
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																																				
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																																				
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																																				
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																																				
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205135

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	477.6	11.5
10°-20°	1189.2	28.7
20°-30°	1382.3	33.4
30°-40°	846.5	20.4
40°-50°	210.2	5.1
50°-60°	24.6	0.6
60°-70°	9.1	0.2
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3049.1	73.6
0°-40°	3895.6	94.0
0°-60°	4130.4	99.7
0°-90°	4143.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4143.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5185	
5°	5116	478
15°	4268	1189
25°	3059	1382
35°	1325	847
45°	233	210
55°	21	25
65°	11	9
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P205135

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBML1

CANDELA DISTRIBUTION (FULL):

0°	
0°	5184.9
2.5°	5179.6
5°	5115.9
7.5°	4978.1
10°	4792.5
12.5°	4548.7
15°	4267.7
17.5°	3965.5
20°	3668.6
22.5°	3371.7
25°	3059.0
27.5°	2698.5
30°	2284.9
32.5°	1802.5
35°	1325.4
37.5°	933.1
40°	636.2
42.5°	397.6
45°	233.3
47.5°	132.5
50°	68.9
52.5°	31.8
55°	21.2
57.5°	15.9
60°	15.9
62.5°	10.6
65°	10.6
67.5°	5.3
70°	5.3
72.5°	5.3
75°	5.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)