

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203505

Luminaire Tested: **LD6B60D010TE EU6B60709730 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709730 6LBMB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1940.9 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203505

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBMB1

Luminous Intensity Polar Plot






TEST NUMBER: P203505

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	85		88	86	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	81	78
5	93	85	79	75		92	84	79	75		82	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	69	65		83	75	69	65		73	68	65		72	68	65		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	67	61	58		76	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203505

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	11.4
10°-20°	547.1	28.2
20°-30°	658.9	33.9
30°-40°	416.8	21.5
40°-50°	95.4	4.9
50°-60°	1.1	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1427.6	73.6
0°-40°	1844.5	95.0
0°-60°	1940.9	100.0
0°-90°	1940.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1940.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2443	
5°	2388	222
15°	1952	547
25°	1460	659
35°	657	417
45°	105	95
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203505

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2443.4
2.5°	2433.4
5°	2388.2
7.5°	2303.0
10°	2197.6
12.5°	2072.2
15°	1951.7
17.5°	1836.3
20°	1715.9
22.5°	1595.5
25°	1460.0
27.5°	1299.5
30°	1103.8
32.5°	883.1
35°	657.3
37.5°	466.6
40°	316.1
42.5°	195.7
45°	105.4
47.5°	45.2
50°	10.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)