

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204513

Luminaire Tested: **LD6B50D010TE EU6B30508040 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508040 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5068.2 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204513

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204513

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76				76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65				65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204513

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.0	4.2
10°-20°	598.7	11.8
20°-30°	890.7	17.6
30°-40°	1036.4	20.4
40°-50°	1010.2	19.9
50°-60°	777.0	15.3
60°-70°	429.5	8.5
70°-80°	113.8	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1700.4	33.6
0°-40°	2736.9	54.0
0°-60°	4524.1	89.3
0°-90°	5068.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5068.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2236	
5°	2223	211
15°	2120	599
25°	1934	891
35°	1664	1036
45°	1311	1010
55°	867	777
65°	430	430
75°	96	114
85°	0	1
90°	0	



TEST NUMBER: P204513

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2235.8
2.5°	2235.8
5°	2222.9
7.5°	2203.7
10°	2190.8
12.5°	2152.3
15°	2120.1
17.5°	2088.0
20°	2043.0
22.5°	1998.1
25°	1933.8
27.5°	1869.6
30°	1805.3
32.5°	1734.7
35°	1664.0
37.5°	1574.0
40°	1496.9
42.5°	1413.4
45°	1310.6
47.5°	1214.3
50°	1105.0
52.5°	989.4
55°	867.3
57.5°	751.7
60°	642.5
62.5°	533.2
65°	430.5
67.5°	334.1
70°	244.1
72.5°	167.0
75°	96.4
77.5°	45.0
80°	6.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)