

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203711

Luminaire Tested: **LD6B60D010TE EU6B60709730 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709730 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2804.1 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203711

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNH1

Luminous Intensity Polar Plot






TEST NUMBER: P203711

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203711

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.2	11.5
10°-20°	770.9	27.5
20°-30°	883.1	31.5
30°-40°	593.4	21.2
40°-50°	169.5	6.0
50°-60°	41.5	1.5
60°-70°	15.7	0.6
70°-80°	6.1	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1977.2	70.5
0°-40°	2570.6	91.7
0°-60°	2781.6	99.2
0°-90°	2804.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2804.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3595	
5°	3492	323
15°	2766	771
25°	1928	883
35°	946	593
45°	194	170
55°	46	41
65°	15	16
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P203711

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3594.6
2.5°	3569.0
5°	3492.3
7.5°	3354.2
10°	3185.5
12.5°	2970.8
15°	2766.2
17.5°	2551.5
20°	2336.7
22.5°	2132.2
25°	1927.7
27.5°	1738.5
30°	1518.6
32.5°	1227.2
35°	945.9
37.5°	690.3
40°	475.5
42.5°	311.9
45°	194.3
47.5°	117.6
50°	71.6
52.5°	56.2
55°	46.0
57.5°	35.8
60°	25.6
62.5°	20.5
65°	15.3
67.5°	10.2
70°	10.2
72.5°	5.1
75°	5.1
77.5°	5.1
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)