

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205232

Luminaire Tested: **LD6B50D010TE EU6B30508050 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508050 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5591.6 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205232

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205232

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205232

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.0	6.0
10°-20°	1012.9	18.1
20°-30°	1526.9	27.3
30°-40°	1562.8	27.9
40°-50°	910.4	16.3
50°-60°	209.2	3.7
60°-70°	25.7	0.5
70°-80°	6.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2876.8	51.4
0°-40°	4439.6	79.4
0°-60°	5559.2	99.4
0°-90°	5591.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5591.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3493	
5°	3512	337
15°	3588	1013
25°	3347	1527
35°	2536	1563
45°	1173	910
55°	203	209
65°	19	26
75°	6	7
85°	0	0
90°	0	



TEST NUMBER: P205232

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3493.2
2.5°	3486.8
5°	3512.2
7.5°	3537.6
10°	3569.3
12.5°	3575.6
15°	3588.3
17.5°	3575.6
20°	3543.9
22.5°	3442.5
25°	3347.4
27.5°	3195.2
30°	2998.7
32.5°	2795.8
35°	2535.9
37.5°	2244.3
40°	1920.9
42.5°	1559.6
45°	1172.8
47.5°	817.8
50°	538.9
52.5°	342.3
55°	202.9
57.5°	107.8
60°	57.1
62.5°	31.7
65°	19.0
67.5°	19.0
70°	12.7
72.5°	6.3
75°	6.3
77.5°	6.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)