

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204123

Luminaire Tested: **LD6B60D010TE EU6B60709730 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709730 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3217.8 lumens
Efficiency: N/A
Efficacy: 51.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204123

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204123

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	103		109	106	103	101		102	100	98		98	97	95		95	93	92
2	105	99	94	90		102	97	92	89		94	90	87		91	87	85		88	85	83
3	98	90	84	79		96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	83	76	71		90	82	76	71		80	74	70		77	73	69		75	71	68
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	59		80	70	63	59		68	63	58		67	62	58		66	61	57
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50		71	61	54	50		60	54	49		59	53	49		58	53	49
9	69	58	51	46		67	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	47	43		64	54	47	43		53	47	43		52	46	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204123

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.0	7.6
10°-20°	649.5	20.2
20°-30°	867.2	26.9
30°-40°	699.6	21.7
40°-50°	335.3	10.4
50°-60°	198.8	6.2
60°-70°	132.1	4.1
70°-80°	70.8	2.2
80°-90°	19.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1761.8	54.8
0°-40°	2461.4	76.5
0°-60°	2995.5	93.1
0°-90°	3217.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3217.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2639	
5°	2608	245
15°	2312	650
25°	1897	867
35°	1120	700
45°	414	335
55°	220	199
65°	133	132
75°	66	71
85°	15	19
90°	0	



TEST NUMBER: P204123

CATALOG NUMBER: LD6B60D010TE EU6B60709730 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2639.0
2.5°	2639.0
5°	2608.3
7.5°	2557.1
10°	2485.5
12.5°	2408.8
15°	2311.6
17.5°	2219.6
20°	2117.3
22.5°	2009.9
25°	1897.4
27.5°	1779.8
30°	1611.0
32.5°	1375.7
35°	1120.0
37.5°	884.8
40°	685.3
42.5°	531.9
45°	414.3
47.5°	327.3
50°	276.2
52.5°	245.5
55°	219.9
57.5°	199.5
60°	173.9
62.5°	153.4
65°	133.0
67.5°	112.5
70°	97.2
72.5°	81.8
75°	66.5
77.5°	51.1
80°	40.9
82.5°	30.7
85°	15.3
87.5°	5.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)