

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204939

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5684.3 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204939

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204939

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84		99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71		91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61		84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53		77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47		72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41		67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37		62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33		58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30		55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204939

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.0	4.0
10°-20°	646.8	11.4
20°-30°	972.3	17.1
30°-40°	1153.7	20.3
40°-50°	1141.6	20.1
50°-60°	896.8	15.8
60°-70°	502.8	8.8
70°-80°	141.2	2.5
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1846.1	32.5
0°-40°	2999.8	52.8
0°-60°	5038.1	88.6
0°-90°	5684.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5684.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2400	
5°	2396	227
15°	2294	647
25°	2111	972
35°	1850	1154
45°	1487	1142
55°	1011	897
65°	501	503
75°	122	141
85°	0	2
90°	0	



TEST NUMBER: P204939

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2400.2
2.5°	2392.1
5°	2396.2
7.5°	2375.8
10°	2351.3
12.5°	2322.8
15°	2294.3
17.5°	2257.6
20°	2208.7
22.5°	2159.8
25°	2110.9
27.5°	2057.9
30°	1988.7
32.5°	1919.4
35°	1850.1
37.5°	1768.6
40°	1674.9
42.5°	1585.2
45°	1487.4
47.5°	1377.4
50°	1263.3
52.5°	1132.9
55°	1010.6
57.5°	872.1
60°	741.7
62.5°	623.5
65°	501.2
67.5°	395.3
70°	293.4
72.5°	199.7
75°	122.3
77.5°	61.1
80°	16.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)