

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202780

Luminaire Tested: **LD6B60D010TE EU6B60709035 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709035 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4575.7 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202780

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202780

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	101		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	89	83	78		86	81	77			83	79	76			81
4	92	82	75	70	90	81	75	70		79	73	69			77	72	68			75
5	86	75	68	63	84	74	68	63		72	66	62			71	65	61			69
6	80	69	62	57	78	68	61	56		67	61	56			65	60	56			64
7	75	64	56	51	73	63	56	51		62	55	51			60	55	51			59
8	70	59	52	47	69	58	51	47		57	51	46			56	50	46			55
9	66	55	48	43	65	54	47	43		53	47	43			52	47	42			51
10	62	51	44	40	61	50	44	39		50	43	39			49	43	39			48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202780

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.6	5.8
10°-20°	756.4	16.5
20°-30°	1109.0	24.2
30°-40°	1154.2	25.2
40°-50°	798.6	17.5
50°-60°	347.6	7.6
60°-70°	106.6	2.3
70°-80°	32.0	0.7
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2131.9	46.6
0°-40°	3286.1	71.8
0°-60°	4432.3	96.9
0°-90°	4575.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4575.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2822	
5°	2810	267
15°	2686	756
25°	2425	1109
35°	1868	1154
45°	1032	799
55°	374	348
65°	101	107
75°	30	32
85°	6	5
90°	0	



TEST NUMBER: P202780

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2822.2
2.5°	2828.2
5°	2810.4
7.5°	2786.7
10°	2757.0
12.5°	2727.4
15°	2685.9
17.5°	2632.5
20°	2573.2
22.5°	2508.0
25°	2425.0
27.5°	2318.3
30°	2181.9
32.5°	2039.6
35°	1867.7
37.5°	1677.9
40°	1458.5
42.5°	1239.2
45°	1031.7
47.5°	836.0
50°	664.1
52.5°	504.0
55°	373.5
57.5°	266.8
60°	183.8
62.5°	136.4
65°	100.8
67.5°	77.1
70°	53.4
72.5°	41.5
75°	29.6
77.5°	17.8
80°	11.9
82.5°	5.9
85°	5.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)