

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204940

Luminaire Tested: **LD6B60D010TE EU6B60708040 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B60D010TE EU6B60708040 6LBCSMB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5740.9 lumens  
Efficiency: N/A  
Efficacy: 91.9 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204940

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMB1

### Luminous Intensity Polar Plot






TEST NUMBER: P204940

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |  |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0 |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |
| 1   | 111 | 107 | 103 | 100 | 108 | 104 | 101 | 98  | 100 | 98  | 95  | 96  | 94  | 92  | 93  | 91  | 90  | 88  |    |    |   |  |  |  |
| 2   | 102 | 95  | 89  | 84  | 99  | 93  | 87  | 83  | 89  | 85  | 81  | 86  | 82  | 79  | 83  | 80  | 77  | 75  |    |    |   |  |  |  |
| 3   | 93  | 84  | 77  | 71  | 91  | 83  | 76  | 70  | 80  | 74  | 69  | 77  | 72  | 68  | 74  | 70  | 67  | 65  |    |    |   |  |  |  |
| 4   | 86  | 75  | 67  | 61  | 84  | 74  | 66  | 61  | 71  | 65  | 60  | 69  | 63  | 59  | 67  | 62  | 58  | 56  |    |    |   |  |  |  |
| 5   | 79  | 67  | 59  | 53  | 77  | 66  | 59  | 53  | 64  | 57  | 52  | 62  | 56  | 52  | 61  | 55  | 51  | 49  |    |    |   |  |  |  |
| 6   | 74  | 61  | 53  | 47  | 72  | 60  | 52  | 46  | 58  | 51  | 46  | 57  | 50  | 46  | 55  | 50  | 45  | 43  |    |    |   |  |  |  |
| 7   | 68  | 55  | 47  | 41  | 67  | 55  | 47  | 41  | 53  | 46  | 41  | 52  | 45  | 41  | 50  | 45  | 40  | 39  |    |    |   |  |  |  |
| 8   | 64  | 51  | 43  | 37  | 62  | 50  | 42  | 37  | 49  | 42  | 37  | 48  | 41  | 37  | 46  | 41  | 36  | 35  |    |    |   |  |  |  |
| 9   | 60  | 47  | 39  | 33  | 58  | 46  | 39  | 33  | 45  | 38  | 33  | 44  | 38  | 33  | 43  | 37  | 33  | 31  |    |    |   |  |  |  |
| 10  | 56  | 43  | 35  | 30  | 55  | 43  | 35  | 30  | 42  | 35  | 30  | 41  | 34  | 30  | 40  | 34  | 30  | 28  |    |    |   |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204940

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMB1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 229.3  | 4.0       |
| 10°-20°   | 653.2  | 11.4      |
| 20°-30°   | 982.0  | 17.1      |
| 30°-40°   | 1165.1 | 20.3      |
| 40°-50°   | 1153.0 | 20.1      |
| 50°-60°   | 905.7  | 15.8      |
| 60°-70°   | 507.8  | 8.8       |
| 70°-80°   | 142.6  | 2.5       |
| 80°-90°   | 2.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1864.5 | 32.5      |
| 0°-40°    | 3029.6 | 52.8      |
| 0°-60°    | 5088.3 | 88.6      |
| 0°-90°    | 5740.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5740.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2424 |      |
| 5°  | 2420 | 229  |
| 15° | 2317 | 653  |
| 25° | 2132 | 982  |
| 35° | 1868 | 1165 |
| 45° | 1502 | 1153 |
| 55° | 1021 | 906  |
| 65° | 506  | 508  |
| 75° | 124  | 143  |
| 85° | 0    | 2    |
| 90° | 0    |      |



TEST NUMBER: P204940

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2424.1 |
| 2.5°  | 2415.9 |
| 5°    | 2420.0 |
| 7.5°  | 2399.4 |
| 10°   | 2374.7 |
| 12.5° | 2345.9 |
| 15°   | 2317.1 |
| 17.5° | 2280.1 |
| 20°   | 2230.7 |
| 22.5° | 2181.3 |
| 25°   | 2131.9 |
| 27.5° | 2078.4 |
| 30°   | 2008.5 |
| 32.5° | 1938.5 |
| 35°   | 1868.5 |
| 37.5° | 1786.2 |
| 40°   | 1691.5 |
| 42.5° | 1601.0 |
| 45°   | 1502.2 |
| 47.5° | 1391.1 |
| 50°   | 1275.9 |
| 52.5° | 1144.2 |
| 55°   | 1020.7 |
| 57.5° | 880.8  |
| 60°   | 749.1  |
| 62.5° | 629.7  |
| 65°   | 506.2  |
| 67.5° | 399.2  |
| 70°   | 296.3  |
| 72.5° | 201.7  |
| 75°   | 123.5  |
| 77.5° | 61.7   |
| 80°   | 16.5   |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)