

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203187

Luminaire Tested: **LD6B60D010TE EU6B60708040 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708040 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5847.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203187

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203187

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	100		108	105	102	99		101	98	96		97	95	93		93	92	90
2	103	96	90	86		100	94	89	85		91	86	83		88	84	81		85	82	79
3	95	86	80	74		93	85	79	74		82	77	72		80	75	71		77	73	70
4	89	78	71	65		86	77	70	65		75	69	64		72	67	63		70	66	62
5	82	71	64	58		80	70	63	58		68	62	57		66	61	56		65	60	56
6	77	65	57	52		75	64	57	52		63	56	51		61	55	51		60	54	50
7	72	60	52	47		70	59	52	47		58	51	46		56	50	46		55	50	46
8	67	55	48	42		66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	44	39		62	51	44	39		50	43	39		49	43	38		48	42	38
10	60	48	40	36		58	47	40	36		46	40	36		45	40	35		45	39	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203187

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.2	5.3
10°-20°	867.2	14.8
20°-30°	1249.5	21.4
30°-40°	1297.3	22.2
40°-50°	959.1	16.4
50°-60°	572.9	9.8
60°-70°	348.1	6.0
70°-80°	190.7	3.3
80°-90°	53.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2425.9	41.5
0°-40°	3723.1	63.7
0°-60°	5255.2	89.9
0°-90°	5847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5847.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3284	
5°	3262	309
15°	3078	867
25°	2723	1249
35°	2092	1297
45°	1234	959
55°	624	573
65°	348	348
75°	177	191
85°	43	53
90°	0	



TEST NUMBER: P203187

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3283.5
2.5°	3283.5
5°	3262.2
7.5°	3233.8
10°	3191.3
12.5°	3141.6
15°	3077.8
17.5°	3006.9
20°	2936.0
22.5°	2836.7
25°	2723.2
27.5°	2602.7
30°	2446.6
32.5°	2290.6
35°	2092.1
37.5°	1886.4
40°	1659.5
42.5°	1439.6
45°	1234.0
47.5°	1049.6
50°	886.5
52.5°	744.6
55°	624.1
57.5°	531.9
60°	453.9
62.5°	397.1
65°	347.5
67.5°	304.9
70°	262.4
72.5°	219.8
75°	177.3
77.5°	141.8
80°	106.4
82.5°	78.0
85°	42.6
87.5°	21.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)