

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204633

Luminaire Tested: **LD6B60D010TE EU6B60709027 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709027 6LB5MW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5327.7 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204633

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204633

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204633

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.4	3.8
10°-20°	579.7	10.9
20°-30°	873.1	16.4
30°-40°	1038.9	19.5
40°-50°	1037.1	19.5
50°-60°	843.4	15.8
60°-70°	518.8	9.7
70°-80°	201.0	3.8
80°-90°	32.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1656.3	31.1
0°-40°	2695.2	50.6
0°-60°	4575.6	85.9
0°-90°	5327.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5327.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2146	
5°	2140	203
15°	2058	580
25°	1900	873
35°	1664	1039
45°	1348	1037
55°	944	843
65°	521	519
75°	183	201
85°	25	32
90°	0	



TEST NUMBER: P204633

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2146.5
2.5°	2149.7
5°	2140.2
7.5°	2127.6
10°	2111.8
12.5°	2083.4
15°	2058.1
17.5°	2020.3
20°	1979.2
22.5°	1941.3
25°	1900.3
27.5°	1843.5
30°	1786.7
32.5°	1733.0
35°	1663.6
37.5°	1587.8
40°	1518.4
42.5°	1433.1
45°	1347.9
47.5°	1256.4
50°	1158.5
52.5°	1057.5
55°	943.8
57.5°	833.4
60°	726.0
62.5°	621.9
65°	520.8
67.5°	426.1
70°	337.8
72.5°	255.7
75°	183.1
77.5°	120.0
80°	72.6
82.5°	44.2
85°	25.3
87.5°	12.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)