

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203190

Luminaire Tested: **LD6B60D010TE EU6B60709027 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203190
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709027 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4636.5 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203190

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203190

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	100		108	105	102	99		101	98	96		97	95	93		93	92	90
2	103	96	90	86		100	94	89	85		91	86	83		88	84	81		85	82	79
3	95	86	80	74		93	85	79	74		82	77	72		80	75	71		77	73	70
4	89	78	71	65		86	77	70	65		75	69	64		72	67	63		70	66	62
5	82	71	64	58		80	70	63	58		68	62	57		66	61	56		65	60	56
6	77	65	57	52		75	64	57	52		63	56	51		61	55	51		60	54	50
7	72	60	52	47		70	59	52	47		58	51	46		56	50	46		55	50	46
8	67	55	48	42		66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	44	39		62	51	44	39		50	43	39		49	43	38		48	42	38
10	60	48	40	36		58	47	40	36		46	40	36		45	40	35		45	39	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203190

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.2	5.3
10°-20°	687.6	14.8
20°-30°	990.8	21.4
30°-40°	1028.7	22.2
40°-50°	760.5	16.4
50°-60°	454.3	9.8
60°-70°	276.1	6.0
70°-80°	151.2	3.3
80°-90°	42.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1923.6	41.5
0°-40°	2952.3	63.7
0°-60°	4167.2	89.9
0°-90°	4636.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4636.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2604	
5°	2587	245
15°	2441	688
25°	2159	991
35°	1659	1029
45°	978	761
55°	495	454
65°	276	276
75°	141	151
85°	34	42
90°	0	



TEST NUMBER: P203190

CATALOG NUMBER: LD6B60D010TE EU6B60709027 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2603.7
2.5°	2603.7
5°	2586.8
7.5°	2564.3
10°	2530.6
12.5°	2491.2
15°	2440.6
17.5°	2384.4
20°	2328.1
22.5°	2249.4
25°	2159.4
27.5°	2063.8
30°	1940.1
32.5°	1816.4
35°	1658.9
37.5°	1495.9
40°	1315.9
42.5°	1141.6
45°	978.5
47.5°	832.3
50°	702.9
52.5°	590.5
55°	494.9
57.5°	421.8
60°	359.9
62.5°	314.9
65°	275.6
67.5°	241.8
70°	208.1
72.5°	174.3
75°	140.6
77.5°	112.5
80°	84.4
82.5°	61.9
85°	33.7
87.5°	16.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)