

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203394

Luminaire Tested: **LD6B60D010TE EU6B60708050 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708050 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4880.4 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203394

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBMWH1

Luminous Intensity Polar Plot






TEST NUMBER: P203394

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203394

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	556.6	11.4
10°-20°	1366.5	28.0
20°-30°	1581.0	32.4
30°-40°	1010.6	20.7
40°-50°	286.5	5.9
50°-60°	51.1	1.0
60°-70°	20.9	0.4
70°-80°	7.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3504.1	71.8
0°-40°	4514.7	92.5
0°-60°	4852.3	99.4
0°-90°	4880.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4880.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6088	
5°	5980	557
15°	4901	1366
25°	3489	1581
35°	1595	1011
45°	333	287
55°	48	51
65°	20	21
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P203394

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6088.4
2.5°	6081.6
5°	5979.8
7.5°	5796.5
10°	5538.6
12.5°	5240.0
15°	4900.6
17.5°	4547.6
20°	4201.5
22.5°	3862.1
25°	3488.8
27.5°	3081.5
30°	2626.8
32.5°	2117.7
35°	1595.1
37.5°	1153.9
40°	800.9
42.5°	529.4
45°	332.6
47.5°	196.8
50°	115.4
52.5°	67.9
55°	47.5
57.5°	40.7
60°	33.9
62.5°	27.2
65°	20.4
67.5°	13.6
70°	13.6
72.5°	6.8
75°	6.8
77.5°	6.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)