

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204225

Luminaire Tested: **LD6B60D010TE EU6B60709727 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709727 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4442.4 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204225

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204225

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204225

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.6	4.9
10°-20°	591.5	13.3
20°-30°	821.5	18.5
30°-40°	896.4	20.2
40°-50°	836.2	18.8
50°-60°	634.7	14.3
60°-70°	347.5	7.8
70°-80°	95.6	2.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1630.6	36.7
0°-40°	2527.0	56.9
0°-60°	3997.9	90.0
0°-90°	4442.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4442.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2323	
5°	2304	218
15°	2108	592
25°	1785	821
35°	1433	896
45°	1086	836
55°	709	635
65°	347	348
75°	83	96
85°	0	1
90°	0	



TEST NUMBER: P204225

CATALOG NUMBER: LD6B60D010TE EU6B60709727 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2323.4
2.5°	2323.4
5°	2303.8
7.5°	2274.5
10°	2230.4
12.5°	2171.7
15°	2108.2
17.5°	2029.9
20°	1956.5
22.5°	1868.5
25°	1785.3
27.5°	1702.2
30°	1609.2
32.5°	1521.2
35°	1433.2
37.5°	1345.1
40°	1262.0
42.5°	1173.9
45°	1085.9
47.5°	997.8
50°	900.0
52.5°	807.1
55°	709.2
57.5°	616.3
60°	523.4
62.5°	430.4
65°	347.3
67.5°	269.0
70°	200.5
72.5°	137.0
75°	83.2
77.5°	39.1
80°	9.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)