

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205346

Luminaire Tested: **LD6B60D010TE EU6B60708050 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708050 6LBNI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4915.9 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205346

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNLI1

Luminous Intensity Polar Plot






TEST NUMBER: P205346

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	109	107	106		105	104	102		102	101	99		98	97	96
2	109	105	101	98	107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	94	91	103	97	93	90		95	91	89		93	90	87		90	88	86
4	100	93	88	85	98	92	88	84		90	86	83		88	85	82		86	84	81
5	96	88	83	79	94	87	83	79		86	82	78		84	81	78		83	80	77
6	92	84	79	75	90	83	78	75		82	77	74		80	76	74		79	76	73
7	88	80	74	71	87	79	74	71		78	73	70		77	73	70		76	72	69
8	84	76	71	67	83	75	70	67		74	70	67		73	69	66		73	69	66
9	81	73	67	64	80	72	67	64		71	67	63		70	66	63		70	66	63
10	78	69	64	61	77	69	64	61		68	64	61		67	63	60		67	63	60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205346

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	930.6	18.9
10°-20°	1670.3	34.0
20°-30°	1350.5	27.5
30°-40°	778.0	15.8
40°-50°	164.5	3.3
50°-60°	14.2	0.3
60°-70°	7.0	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3951.3	80.4
0°-40°	4729.2	96.2
0°-60°	4907.9	99.8
0°-90°	4915.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4915.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11192	
5°	10427	931
15°	6068	1670
25°	2913	1350
35°	1233	778
45°	177	164
55°	14	14
65°	7	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205346

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	11192.3
2.5°	11057.7
5°	10426.8
7.5°	9519.5
10°	8406.7
12.5°	7265.4
15°	6067.5
17.5°	4912.2
20°	4068.7
22.5°	3423.6
25°	2913.3
27.5°	2480.9
30°	2091.0
32.5°	1658.6
35°	1233.4
37.5°	857.7
40°	560.0
42.5°	340.2
45°	177.2
47.5°	70.9
50°	21.3
52.5°	21.3
55°	14.2
57.5°	14.2
60°	7.1
62.5°	7.1
65°	7.1
67.5°	7.1
70°	7.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)