

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205449

Luminaire Tested: **LD6B60D010TE EU6B60708050 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708050 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6665.4 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205449

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSLI1

Luminous Intensity Polar Plot






TEST NUMBER: P205449

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			94
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			85
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			77
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			70
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			64
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			59
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			54
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			50
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			47
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205449

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.6	5.8
10°-20°	986.7	14.8
20°-30°	1258.3	18.9
30°-40°	1304.9	19.6
40°-50°	1202.4	18.0
50°-60°	904.4	13.6
60°-70°	488.2	7.3
70°-80°	131.0	2.0
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2632.6	39.5
0°-40°	3937.5	59.1
0°-60°	6044.3	90.7
0°-90°	6665.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6665.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4206	
5°	4142	388
15°	3519	987
25°	2733	1258
35°	2082	1305
45°	1565	1202
55°	1013	904
65°	489	488
75°	113	131
85°	0	2
90°	0	



TEST NUMBER: P205449

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4206.2
2.5°	4192.0
5°	4142.5
7.5°	4050.4
10°	3887.5
12.5°	3724.7
15°	3519.3
17.5°	3328.1
20°	3129.9
22.5°	2924.5
25°	2733.3
27.5°	2549.2
30°	2379.3
32.5°	2223.5
35°	2081.9
37.5°	1947.3
40°	1819.9
42.5°	1685.3
45°	1564.9
47.5°	1430.4
50°	1295.8
52.5°	1154.2
55°	1012.6
57.5°	871.0
60°	736.4
62.5°	609.0
65°	488.6
67.5°	375.3
70°	276.2
72.5°	191.2
75°	113.3
77.5°	49.6
80°	14.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)