

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204938

Luminaire Tested: **LD6B60D010TE EU6B60708030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5542.3 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204938

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBCSMB1

Luminous Intensity Polar Plot




TEST NUMBER: P204938
CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	111	107	103	100		108	104	101	98		100	98	95		96	94	92		93	91	90	88
2	102	95	89	84		99	93	87	83		89	85	81		86	82	79		83	80	77	75
3	93	84	77	71		91	83	76	70		80	74	69		77	72	68		74	70	67	65
4	86	75	67	61		84	74	66	61		71	65	60		69	63	59		67	62	58	56
5	79	67	59	53		77	66	59	53		64	57	52		62	56	52		61	55	51	49
6	74	61	53	47		72	60	52	46		58	51	46		57	50	46		55	50	45	43
7	68	55	47	41		67	55	47	41		53	46	41		52	45	41		50	45	40	39
8	64	51	43	37		62	50	42	37		49	42	37		48	41	37		46	41	36	35
9	60	47	39	33		58	46	39	33		45	38	33		44	38	33		43	37	33	31
10	56	43	35	30		55	43	35	30		42	35	30		41	34	30		40	34	30	28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204938

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.4	4.0
10°-20°	630.6	11.4
20°-30°	948.0	17.1
30°-40°	1124.8	20.3
40°-50°	1113.1	20.1
50°-60°	874.3	15.8
60°-70°	490.2	8.8
70°-80°	137.7	2.5
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1800.0	32.5
0°-40°	2924.8	52.8
0°-60°	4912.2	88.6
0°-90°	5542.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5542.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2340	
5°	2336	221
15°	2237	631
25°	2058	948
35°	1804	1125
45°	1450	1113
55°	985	874
65°	489	490
75°	119	138
85°	0	2
90°	0	



TEST NUMBER: P204938

CATALOG NUMBER: LD6B60D010TE EU6B60708030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2340.3
2.5°	2332.3
5°	2336.3
7.5°	2316.4
10°	2292.6
12.5°	2264.8
15°	2237.0
17.5°	2201.2
20°	2153.5
22.5°	2105.8
25°	2058.2
27.5°	2006.5
30°	1939.0
32.5°	1871.4
35°	1803.9
37.5°	1724.4
40°	1633.0
42.5°	1545.6
45°	1450.2
47.5°	1343.0
50°	1231.7
52.5°	1104.6
55°	985.4
57.5°	850.3
60°	723.1
62.5°	607.9
65°	488.7
67.5°	385.4
70°	286.1
72.5°	194.7
75°	119.2
77.5°	59.6
80°	15.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)