

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203503

Luminaire Tested: **LD6B60D010TE EU6B60709050 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709050 6LBMB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2265.9 lumens
Efficiency: N/A
Efficacy: 36.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203503

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P203503

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106		111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96		106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88		101	95	91	87		93	89	86			90	87	85			88
4	98	91	85	81		96	90	85	81		87	83	80			85	82	79			84
5	93	85	79	75		92	84	79	75		82	78	74			81	77	74			79
6	89	80	74	70		87	79	74	70		78	73	69			76	72	69			75
7	84	75	69	65		83	75	69	65		73	68	65			72	68	65			71
8	80	71	65	61		79	71	65	61		69	64	61			68	64	61			67
9	77	67	61	58		76	67	61	57		66	61	57			65	60	57			64
10	73	64	58	54		72	63	58	54		62	57	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203503

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.8	11.4
10°-20°	638.7	28.2
20°-30°	769.3	33.9
30°-40°	486.6	21.5
40°-50°	111.3	4.9
50°-60°	1.3	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1666.7	73.6
0°-40°	2153.3	95.0
0°-60°	2265.9	100.0
0°-90°	2265.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2265.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2853	
5°	2788	259
15°	2279	639
25°	1704	769
35°	767	487
45°	123	111
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203503

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2852.6
2.5°	2840.9
5°	2788.2
7.5°	2688.6
10°	2565.6
12.5°	2419.1
15°	2278.6
17.5°	2143.8
20°	2003.3
22.5°	1862.7
25°	1704.5
27.5°	1517.1
30°	1288.6
32.5°	1030.9
35°	767.3
37.5°	544.7
40°	369.0
42.5°	228.4
45°	123.0
47.5°	52.7
50°	11.7
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)