

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204634

Luminaire Tested: **LD6B60D010TE EU6B60709030 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709030 6LB5MW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5539.3 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204634

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204634

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204634

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.5	3.8
10°-20°	602.8	10.9
20°-30°	907.8	16.4
30°-40°	1080.2	19.5
40°-50°	1078.2	19.5
50°-60°	876.9	15.8
60°-70°	539.5	9.7
70°-80°	209.0	3.8
80°-90°	33.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1722.1	31.1
0°-40°	2802.3	50.6
0°-60°	4757.4	85.9
0°-90°	5539.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5539.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2232	
5°	2225	211
15°	2140	603
25°	1976	908
35°	1730	1080
45°	1401	1078
55°	981	877
65°	542	539
75°	190	209
85°	26	33
90°	0	



TEST NUMBER: P204634

CATALOG NUMBER: LD6B60D010TE EU6B60709030 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2231.8
2.5°	2235.1
5°	2225.2
7.5°	2212.1
10°	2195.7
12.5°	2166.2
15°	2139.9
17.5°	2100.5
20°	2057.9
22.5°	2018.5
25°	1975.8
27.5°	1916.7
30°	1857.7
32.5°	1801.9
35°	1729.7
37.5°	1650.9
40°	1578.7
42.5°	1490.1
45°	1401.4
47.5°	1306.3
50°	1204.5
52.5°	1099.5
55°	981.3
57.5°	866.5
60°	754.9
62.5°	646.6
65°	541.5
67.5°	443.1
70°	351.2
72.5°	265.8
75°	190.4
77.5°	124.7
80°	75.5
82.5°	45.9
85°	26.3
87.5°	13.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)