

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203812

Luminaire Tested: **LD6B60D010TE EU6B60709050 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709050 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3506.2 lumens
Efficiency: N/A
Efficacy: 56.1 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203812

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203812

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94
3	104	98	93	90	102	97	92	89	94	91	88		92	89	86		89
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203812

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.7	16.6
10°-20°	1119.7	31.9
20°-30°	1017.9	29.0
30°-40°	617.0	17.6
40°-50°	140.5	4.0
50°-60°	17.9	0.5
60°-70°	8.1	0.2
70°-80°	2.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2720.4	77.6
0°-40°	3337.4	95.2
0°-60°	3495.8	99.7
0°-90°	3506.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3506.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6884	
5°	6490	583
15°	4032	1120
25°	2207	1018
35°	978	617
45°	155	140
55°	18	18
65°	6	8
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P203812

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6883.7
2.5°	6800.2
5°	6490.0
7.5°	5988.9
10°	5350.7
12.5°	4688.6
15°	4032.4
17.5°	3435.9
20°	2934.8
22.5°	2529.2
25°	2207.1
27.5°	1920.8
30°	1640.4
32.5°	1312.3
35°	978.3
37.5°	686.0
40°	453.3
42.5°	280.4
45°	155.1
47.5°	71.6
50°	29.8
52.5°	23.9
55°	17.9
57.5°	17.9
60°	11.9
62.5°	11.9
65°	6.0
67.5°	6.0
70°	6.0
72.5°	6.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)