

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204852

Luminaire Tested: **LD6B70D010TE EU6B60709024 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204852  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709024 6LBCSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5625.4 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204852

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204852

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBSCMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204852

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	217.7	3.9
10°-20°	619.7	11.0
20°-30°	932.3	16.6
30°-40°	1104.9	19.6
40°-50°	1099.5	19.5
50°-60°	886.4	15.8
60°-70°	536.2	9.5
70°-80°	199.1	3.5
80°-90°	29.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1769.7	31.5
0°-40°	2874.6	51.1
0°-60°	4860.5	86.4
0°-90°	5625.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5625.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2298	
5°	2287	218
15°	2195	620
25°	2025	932
35°	1769	1105
45°	1432	1100
55°	989	886
65°	539	536
75°	181	199
85°	24	30
90°	0	



TEST NUMBER: P204852

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2297.6
2.5°	2297.6
5°	2287.4
7.5°	2280.5
10°	2260.1
12.5°	2226.0
15°	2195.3
17.5°	2161.2
20°	2120.3
22.5°	2079.4
25°	2024.9
27.5°	1966.9
30°	1902.2
32.5°	1840.8
35°	1769.2
37.5°	1694.2
40°	1605.6
42.5°	1520.4
45°	1431.7
47.5°	1332.9
50°	1223.8
52.5°	1111.3
55°	988.6
57.5°	879.5
60°	756.8
62.5°	647.7
65°	538.6
67.5°	436.3
70°	340.9
72.5°	255.7
75°	180.7
77.5°	115.9
80°	68.2
82.5°	40.9
85°	23.9
87.5°	10.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)