

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204129

Luminaire Tested: **LD6B70D010TE EU6B60709024 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709024 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3696.8 lumens
Efficiency: N/A
Efficacy: 46.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204129

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204129

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204129

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.5	7.6
10°-20°	746.2	20.2
20°-30°	996.3	26.9
30°-40°	803.8	21.7
40°-50°	385.2	10.4
50°-60°	228.3	6.2
60°-70°	151.8	4.1
70°-80°	81.3	2.2
80°-90°	22.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2024.0	54.8
0°-40°	2827.8	76.5
0°-60°	3441.3	93.1
0°-90°	3696.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3696.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3032	
5°	2996	282
15°	2656	746
25°	2180	996
35°	1287	804
45°	476	385
55°	253	228
65°	153	152
75°	76	81
85°	18	22
90°	0	



TEST NUMBER: P204129

CATALOG NUMBER: LD6B70D010TE EU6B60709024 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3031.8
2.5°	3031.8
5°	2996.5
7.5°	2937.7
10°	2855.5
12.5°	2767.4
15°	2655.7
17.5°	2550.0
20°	2432.5
22.5°	2309.1
25°	2179.8
27.5°	2044.7
30°	1850.8
32.5°	1580.5
35°	1286.7
37.5°	1016.5
40°	787.3
42.5°	611.1
45°	475.9
47.5°	376.0
50°	317.3
52.5°	282.0
55°	252.6
57.5°	229.1
60°	199.8
62.5°	176.3
65°	152.8
67.5°	129.3
70°	111.6
72.5°	94.0
75°	76.4
77.5°	58.8
80°	47.0
82.5°	35.3
85°	17.6
87.5°	5.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)