

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204956

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204956
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709027 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5402.8 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204956

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204956

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204956

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.8	4.0
10°-20°	614.8	11.4
20°-30°	924.2	17.1
30°-40°	1096.5	20.3
40°-50°	1085.1	20.1
50°-60°	852.3	15.8
60°-70°	477.9	8.8
70°-80°	134.2	2.5
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.7	32.5
0°-40°	2851.2	52.8
0°-60°	4788.7	88.6
0°-90°	5402.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5402.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2281	
5°	2278	216
15°	2181	615
25°	2006	924
35°	1758	1097
45°	1414	1085
55°	961	852
65°	476	478
75°	116	134
85°	0	2
90°	0	



TEST NUMBER: P204956

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2281.4
2.5°	2273.7
5°	2277.5
7.5°	2258.2
10°	2234.9
12.5°	2207.8
15°	2180.7
17.5°	2145.8
20°	2099.4
22.5°	2052.9
25°	2006.4
27.5°	1956.0
30°	1890.2
32.5°	1824.3
35°	1758.5
37.5°	1681.0
40°	1591.9
42.5°	1506.7
45°	1413.8
47.5°	1309.2
50°	1200.7
52.5°	1076.8
55°	960.6
57.5°	828.9
60°	704.9
62.5°	592.6
65°	476.4
67.5°	375.7
70°	278.9
72.5°	189.8
75°	116.2
77.5°	58.1
80°	15.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)